

TECHSPEC[®] 40mm - 65mm Length, T-Mount Fine Focus Tube



Stock #58-755 20+ In Stock

-

1

+

C\$176^{.40}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$176.40 each
Qty 5-9	C\$156.24 each
Qty 10-25	C\$144.34 each
Need More?	Request Quote

Product Downloads

General	
Type:	
Fine Focus Tube	
Function:	
Extension Tube (Adjustable)	
Physical & Mechanical Properties	
Extension Length (mm):	
40.0 - 65.0	

48.0	Outer Diameter (mm):
33.0	Clear Aperture CA (mm):
Threading & Mounting	
M33 x0.5	Barrel Thread:
T-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

- Finely Threaded Internal Barrel for Fine Focus Adjustments
- Inner Diameter Baffle Thread for Stray Light Reduction
- Knurled Lip on Female End for Controlled Adjustments

TECHSPEC® C, S, and T-Mount Fine Thread Focus Tubes are used for making precision adjustments to optical element positions within a system. These tubes feature an outer barrel with male C, S, or T-Mount thread at the base end and a finely threaded interior barrel to allow for fine focusing. The secondary barrel has a female S, C, or T-Mount thread, knurled ring at the front end for easy adjustment, and a threaded interior for light baffle. Set screws can be used to fix the extension position. TECHSPEC C, S, and T-Mount Fine Thread Focus Tubes offer different extension length options to meet specific application demands.

Note: Compatible Allen wrenches for C, S, and T-Mount Fine Thread Focus Tubes ([#56-271](#), [#55-452](#), and [#58-637](#), respectively) sold separately.

Technical Information

