

40 lp/mm, 1" x 3", FS w/ Fluorescent, Ronchi



Stock **#57-877** CLEARANCE **5 In Stock**

-

1

+

C\$590^{.80}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$590.80 each
Qty 5+	C\$561.82 each
Need More?	Request Quote

Product Downloads

Physical & Mechanical Properties	
3.00	Length (inches):
12.7 x25.4	Pattern Size (mm):
1.10	Thickness (mm):
1.00	Width (inches):
Optical Properties	

Coating:	
Vacuum Deposited Chrome Fluorescent Peak Excitation @ 365 nm; Fluorescent Peak Emission @ 550 nm	
Frequency (lp/mm):	
40.00	
Substrate:	
Fused Silica with Fluorescent Backing	
Optical Density OD (Average):	
3.00	
Regulatory Compliance	
RoHS 2015:	
Compliant	
Certificate of Conformance:	
View	
Reach 240:	
Compliant	

Product Details

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
 - Ideal for Reticle and Field Calibration Requirements
 - Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).
- Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.