

4.0 OD M105 x 1.00, Machine Vision Absorptive ND Filter



Stock **#21-620** ☐ In Stock

-

1

+

C\$722.40

ADD TO CART

Qty 1-9
C\$722.40
Qty 10+
C\$686.42
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
100.00

Filter Thread:
M105 x 1.00

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.8
Mount Thickness Including Threads (mm): 8.6

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
