

4.0 OD M39 x 0.50, Machine Vision Absorptive ND Filter



Stock **#21-433** ☐ In Stock

-

1

+

C\$166.60

ADD TO CART

Qty 1-9
C\$166.60
Qty 10+
C\$158.76
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
34.00

Filter Thread:
M39 x0.50

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%): 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 5.2
Mount Thickness Including Threads (mm): 7.0

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
