

4.0 OD M72 x 0.75, Machine Vision Absorptive ND Filter



Stock **#21-603** ☐ In Stock

-

1

+

C\$263.20

ADD TO CART

Qty 1-9
C\$263.20
Qty 10+
C\$249.76
Volume Pricing
Request Quote

Get Product Downloads

Optical Density OD (Average):
4.0

Clear Aperture CA (mm):
67.50

Filter Thread:
M72 x0.75

Substrate: ☐
ND Filter Glass

Surface Quality: 40-20
Transmission (%) : 0.01
Type: Mounted Imaging Filter
Blocking Wavelength Range (nm): 425 - 675
Mount Thickness (mm): 6.0
Mount Thickness Including Threads (mm): 8.3

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
