

TECHSPEC® 400-700nm OD 0.1, M30.5 x 0.5 Absorptive ND Filter



Stock **#66-714** [CONTACT US](#)

- 1 + **C\$109.20**

ADD TO CART

Qty 1-9
C\$109.20
Qty 10+
C\$101.92
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
33.50

Optical Density OD (Average):
0.1

Clear Aperture CA (mm):
22.0

Filter Thread:
M30.5 x0.50

Substrate: ND Filter Glass
Coating: Uncoated
Transmission (%): 79.00
Type: Neutral Density Filter
Stock No. of Unmounted Filter: #63-460
Mount Thickness (mm): 9.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Exempt
Certificate of Conformance: View