

TECHSPEC[®] 40.0mm Dia. x 200.0mm FL, Uncoated, Plano-Convex Lens



Stock **#33-376** ☐ In Stock

[Other Coating Options](#)

-

1

+

C\$58.10

ADD TO CART

Qty 1-9
C\$58.10
Qty 10+
C\$52.15
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
40.00 +0.0/-0.025

Effective Focal Length EFL (mm):
200.00 @ 587.6nm

Back Focal Length BFL (mm): 196.7
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 5.00 ±0.10
Edge Thickness ET (mm): 3.05
Radius R₁ (mm): 103.36
Clear Aperture CA (mm): 39
f#: 5
Numerical Aperture NA: 0.10
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 330 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 211: Compliant
Certificate of Conformance: View