

405nm, $\lambda/2$ Polymer Waveplate



Polymer Waveplates (Retarders)

Stock **#91-011** ☐ In Stock

-

1

+

C\$603.40

ADD TO CART

Qty 1-5
C\$603.40
Qty 6+
C\$483.00
Volume Pricing
Request Quote

Get Product Downloads

Coating: R _{avg} <0.5% @ 400 - 700nm
Design Wavelength DWL (nm): 405
Diameter (mm): 25.00
Substrate: ☐

[B270](#)

Retardance:

$\lambda/2$

Thickness (mm):

2.00

Thickness Tolerance (mm):

± 0.2

Type:

Polymer Waveplate

Parallelism (arcmin):

3.00

Dimensional Tolerance (mm):

+0.0/-0.2

Construction:

Birefringent Polymer Stack

Retardance Tolerance (nm):

$\pm 10 @ 405$

Retardance Order:

0

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Reach 224:

[Compliant](#)

Certificate of Conformance:

[View](#)