

408 x 609mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock #85-207 ☐ In Stock

-

1

+

C\$562.80

ADD TO CART

Qty 1-5

C\$562.80

Qty 6+

C\$450.10

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):

4 - 6λ

Substrate: ☐

Float Glass

Surface Quality:

80-50

Dimensions (mm):

408.0 x609.0 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 609.00
Width (mm): 408.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant