

TECHSPEC® 40mm, Center Drive, Standard Top, English Micrometer Stage



Stock **#66-403** **3 In Stock**

⊖ 1 ⊕ **CS613²⁰**

ADD TO CART

Volume Pricing	
Qty 1-2	CS613.20 each
Qty 3+	CS534.80 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

Linear (X) **Type of Movement:**

Crossed Roller Bearing **Guide System:**

Center Drive **Drive Orientation:**

30mm Standard-Top Stages - Center Drive



30mm Standard-Top Stages - Side Drive



40mm Standard-Top Stages - Center Drive



40mm Standard-Top Stages - Side Drive



70mm Standard-Top Stages - Center Drive



70mm Standard-Top Stages - Side Drive



125mm Standard-Top Stages - Center Drive



125mm Standard-Top Stages - Side Drive

