

[See all 6 Products in Family](#)

## 40mm Dia. x 200mm FL Uncoated, DCX N-K5 Lens



Stock #32-910 CLEARANCE **20+ In Stock**

[Other Coating Options](#)

1  CS31<sup>.50</sup>

ADD TO CART

### Volume Pricing

Qty 1+	C\$31.50 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

#### General

Double-Convex Lens Type:

#### Physical & Mechanical Properties

40.00 +0.00/-0.10 Diameter (mm):

<1 Centering (arcmin):

8.00 ±0.10 Center Thickness CT (mm):


6.07	Edge Thickness ET (mm):
39	Clear Aperture CA (mm):
Protective as needed	Bevel:
<b>Optical Properties</b>	
200.00 @ 587.6nm	Effective Focal Length EFL (mm):
197.36	Back Focal Length BFL (mm):
Uncoated	Coating:
N-K5	Substrate: <input type="checkbox"/>
40-20	Surface Quality:
1.5λ	Power (P-V) @ 632.8nm:
λ/4	Irregularity (P-V) @ 632.8nm:
±1	Focal Length Tolerance (%):
5.00	f#:
0.10	Numerical Aperture NA:
330 - 2500	Wavelength Range (nm):

<b>Regulatory Compliance</b>	
<a href="#">View</a>	Certificate of Conformance:

### Product Details

- N-K5 Substrate
  - Various Anti-Reflection (AR) Coatings
  - PCX and DCX Options Available
- N-K5 Lenses are available in various diameters, focal lengths, as well as Plano-Convex and Double-Convex form factors. Anti-reflective coatings covering the VIS to NIR make these ideal for multiple applications.

### Technical Information



### Compatible Mounts