

4.0mm Diameter, Ruby Half-Ball Lens



Stock **#49-562** ☐ In Stock

1

C\$39.90

ADD TO CART

Qty 1-10
C\$39.90
Qty 11+
C\$31.50
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):

4.00

Substrate: ☐

RubyDoped Sapphire (Al₂O₃)

Coating:

Uncoated

Type:

Half-Ball Lens
Index of Refraction n_d: 1.77
Melting Temperature (°C): 2053.00
Radius R (mm): 2.00
Specific Gravity (g/cm³): 3.98
Sphericity (µm): 0.64
Thickness (mm): 2.00
Compressive Strength (psi): 300,000
Diameter Tolerance (µm): ±2.54

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant