

TECHSPEC[®] 40mm Length, C-Mount Extension Tube



Stock **#54-631** 20+ In Stock

-

1

+

C\$73^{.50}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$73.50 each
Qty 5-9	C\$65.24 each
Qty 10-25	C\$60.34 each
Need More?	Request Quote

Product Downloads

General

Type:

Extension Tube

Function:

Extension Tube (Fixed)

Physical & Mechanical Properties

Extension Length (mm):

40.0

44.0	Total Length (mm):
30.0	Outer Diameter (mm):
22.0	Clear Aperture CA (mm):

Threading & Mounting

C-Mount	Thread Type:
---------	--------------

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	REACH 241:

Product Details

- Used for Adding a Fixed Tube Extension to Optical Systems
- Feature Male/Female Threads at Opposite Ends
- Black Anodized Aluminum Construction

TECHSPEC® C, S, and T-Mount Extension Tubes add extension length to an optical system while blocking external light and debris from entering the system. Extension tubes are available with C, S, or T-Mount threading, allowing them to be integrated into a wide range of systems and applications. Their black anodized aluminum construction, combined with a threaded inner diameter, ensures that stray light is reduced within the system. TECHSPEC C, S, and T-Mount Extension Tubes feature different lengths that can be combined to create the exact extension length needed for a specific application. The actual tube length is longer than the extension length due to the male threaded portion.

Technical Information

