

TECHSPEC[®] 40mm, Metric Rotary Stage



Stock **#66-515** 8 In Stock

-

1

+

C\$576^{.80}

ADD TO CART

Volume Pricing	
Qty 1-2	C\$576.80 each
Qty 3+	C\$503.86 each
Need More?	Request Quote

Product Downloads

General

Type:
Metric

Note:
[Bottom adapter plate](#), sold separately, is required to mount 30mm and 40mm stages to a standard breadboard.

Physical & Mechanical Properties

Type of Movement:
Rotary

Slide-Fit	Guide System:
40 Dia.	Stage Size (mm):
±5 (Fine), 360 (Coarse)	Travel (°):
50	Concentricity (µm):
Aluminium Stage	Construction:
10	Increments (arcmin):
1.5	Load Capacity (kg):
30	Parallelism (µm):
0.1	Weight (kg):
20	Wobble (µm):

Hardware & Interface Connectivity

Metric Micrometer	Type of Drive:

Threading & Mounting

(1) M6 x 1, (8) M2 x 0.4	Mounting Threads:

Regulatory Compliance

Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details

- Low Profile Design
- Precision Micrometer Drive
- Slide-Fit Guide System
- 360° Coarse Rotation, ±5° Total Fine Rotation
- Mechanically Compatible to Other TECHSPEC® Stages
- Locking Screw on All Stages
- Class 100 (ISO 5) Clean Room Compatible

TECHSPEC® Rotary Stages provide smooth, coarse rotary movement and feature a precision micrometer drive for fine adjustment. This allows for quick rotation over 360° travel and precise angular adjustment at any position. Stage position can be fixed using the locking mechanism. TECHSPEC Rotary Stages are available in four sizes: 30mm, 40mm, 70mm, and 125mm diameters. Each stage is available in English or Metric standards. Each stage is designed to integrate with TECHSPEC® components, further enhancing flexibility and allowing the user to create any number of axes in different configurations. A [bottom adapter plate](#), sold separately, is required to mount 30mm and 40mm stages to a standard breadboard; 70mm and 125mm stages can be mounted directly to the board.

Technical Information



