

TECHSPEC[®] 40mm Square Magnetic Base, Metric



#19-286 - 40mm Square Magnetic Base, Metric

Stock **#19-286** 8 In Stock

-

1

+

C\$191¹⁰

ADD TO CART

Volume Pricing	
Qty 1-9	C\$191.10 each
Qty 10+	C\$171.99 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Metric

Type:

Note:

The permanent magnet is turned on and off by a switching lever

Physical & Mechanical Properties	
20.00	Thickness (mm):
40.00	Width (mm):
0.22	Weight (kg):
Anodized Aluminum	Construction:
40.00	Length (mm):
Threading & Mounting	
(8) M2 x 0.4, (4) M3 x 0.5, (1) M6 x 1.0	Mounting Threads:
Material Properties	
49	Magnetic Force (N):
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:

PRODUCT DETAILS

- On/Off Magnet for Easy Placement on Lab Bench
- Low Profile 20mm Height
- Compatible with [TECHSPEC Stages](#)

TECHSPEC® Low Profile Magnetic Bases are ideal for placing benchtop system components and subassemblies anywhere on a lab table with ease. Designed to complement our [TECHSPEC Stages](#), these magnetic bases add just 20mm in height, enabling easy integration without compensation for the height of other optics and subassemblies. Switchable magnets providing 49 or 196N allow for easily securing subassemblies in place and for removing them when no longer required. TECHSPEC Low Profile Magnetic Bases share the same hole patterns as our TECHSPEC stages, making them an ideal lab bench component for system building.