

[See all 7 Products in Family](#)

40X Microscope/ 8 X 30 Scope



Stock **#54-915** **1 In Stock**

-

1

+

C\$488^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	C\$488.60 each
Qty 5+	C\$462.42 each
Need More?	Request Quote

Product Downloads

General

Note:

Micro Length: 213
Scope Length: 130

Physical & Mechanical Properties

Diameter (mm):
42.00

Field of View (mm):
Micro: 8.0, Scope: 72 - 8.5°

Weight (g):

Micro: 228, Scope: 170

Optical Properties

Magnification:

Micro: 40X, Scope: 13.5 - 8X

Working Distance (mm):

Micro: 65, Scope: 600 - ∞

Regulatory Compliance

Certificate of Conformance:

[View](#)

Product Details

- 25X, 30X, 35X, 40X, 45XModels
- Close Focus and Long Distance Ranges
- True Erect Images
- C-mount Camera Adapter for 25Xand 35XModels

Close Focus Dual Purpose Microscopes are ideal for multi-purpose inspection applications. Internal roof prism ensures crisp, erect images. Each scope includes object adjustment with a smooth, spiral twist focus ring. Close Focus Dual Purpose Microscopes feature a clear acrylic base that allows the instrument to rest directly on a flat object while passing ambient light. Two cutaways, opposite each other, in the clear base, allow fine instruments to manipulate the object under inspection. The base can be removed for irregular objects. The base and bottom macro lens can be removed for added flexibility as an erect-image monocular scope for long-distance requirements. The C-mount Camera Adapter for video-imaging applications using the 35Xmodel fits with setscrews over the eyepiece, while the 25Xversion threads onto the scope. Note that additional fine focus ring is only provided on macro lens with 45Xand 40Xmodels. A padded storage case is included.