

41 x 63.5mm AR Coated Float Glass Window



Stock #32-740 **20+ In Stock**

- 1 + C\$38¹⁵

ADD TO CART

Volume Pricing

Qty 1-5	C\$38.15 each
Qty 6-49	C\$33.60 each
Qty 50-99	C\$32.20 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

41.00 x 63.50 **Dimensions (mm):**

3.00 (nominal)	Thickness (mm):
63.50	Length (mm):
41.00	Width (mm):
Fine Ground	Edges:

Optical Properties

BBAR (400-700nm)	Coating:
Float Glass	Substrate: <input type="checkbox"/>
80-50	Surface Quality:
400 - 700	Wavelength Range (nm):
4 - 6λ	Surface Flatness (P-V):

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 247:

Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

Compatible Mounts