

41mm Diameter Float Glass Window



Stock #02-207 **20+ In Stock**

- 1 + C\$32^{.20}

ADD TO CART

Volume Pricing

Qty 1-5	C\$32.20 each
Qty 6-49	C\$29.40 each
Qty 50-99	C\$28.00 each
Need More?	Request Quote

Product Downloads

General

Protective Window **Type:**
Glass **Type of Window:**

Physical & Mechanical Properties

41.00 **Diameter (mm):**

2.30 **Thickness (mm):**

Fine Ground **Edges:**

Optical Properties

Uncoated **Coating:**

Float Glass **Substrate:** □

80-50 **Surface Quality:**

350 - 2000 **Wavelength Range (nm):**

4 - 6λ **Surface Flatness (P-V):**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 247:**

Product Details

- Transmits Visible and Near Infrared Wavelengths
- Available Uncoated or with an Anti-Reflection Coating
- Variety of Sizes Available

Float Glass Optical Windows are optical glass with polished faces that are relatively parallel and are typically used as a protective element between two environments. Float glass readily transmits visible and near-infrared wavelengths and can be used in a wide variety of applications. Float Glass Optical Windows are versatile products offered in circular and rectangular options. They are available uncoated or with BBAR (Broadband Anti-Reflective) 400-700nm coating.

Compatible Mounts