

25mm Max. Aperture, Iris Diaphragm



Stock **#40-997** ☐ In Stock

-

1

+

C\$130.20

ADD TO CART

Qty 1-4
C\$130.20
Qty 5+
C\$115.36
Volume Pricing
Request Quote

Get Product Downloads

Type:
Unmounted

Minimum Aperture (mm):
1.2

Maximum Aperture (mm):
25.0

Outer Diameter (mm):
42.6

Construction: Brass Housing, Blue Tempered Steel Leaves
Lever Diameter (mm): 5.20
Lever Length (mm): 21.00
Number of Leaves: 10
Thickness (mm): 5.80

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)