

4.4-11mm FL High Resolution Varifocal Lens



#68-665

Stock **#68-665 8 In Stock**

⊖ 1 ⊕ C\$903⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	C\$903.00 each
Need More?	Request Quote

Product Downloads

General

Low Distortion **Note:**
Varifocal Lens **Type:**

Physical & Mechanical Properties

56.50 **Length (mm):**
125.00 **Weight (g):**

45.00 Diameter (mm):

Optical Properties

Field of View @ Min Working Distance (mm):
400 - 175

Horizontal Field of View, 1/2" Sensor:
68.1° - 32.6°

Focal Length Range (mm):
4.4-11

Working Distance (mm):
300 - ∞

Aperture (f/#):
f/1.6 - f/16

Lens Wavelength Range:
VIS

Sensor

Maximum Sensor Format:
1/1.8"

Threading & Mounting

Filter Thread:
M43 x0.75

Mount:
C-Mount

Regulatory Compliance

RoHS 2015:
[Exempt](#)

Certificate of Conformance:
[View](#)

REACH 241:
[Contains SVHC\(s\)](#)

Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.