

4.4-11mm FL High Resolution Varifocal Lens



#68-665

Stock **#68-665** 9 In Stock

-

1

+

C\$903⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$903.00 each
Need More?	Request Quote

Product Downloads

General

Low Distortion	Note:
Varifocal Lens	Type:

Physical & Mechanical Properties

56.50	Length (mm):
125.00	Weight (g):

45.00	Diameter (mm):
Optical Properties	
Field of View @ Min Working Distance (mm): 400 - 175	
Horizontal Field of View, 1/2" Sensor: 68.1° - 32.6°	
Focal Length Range (mm): 4.4-11	
Working Distance (mm): 300 - ∞	
Aperture (f/#): f/1.6 - f/16	
Lens Wavelength Range: VIS	
Sensor	
Maximum Sensor Format: 1/1.8"	
Threading & Mounting	
Filter Thread: M43 x0.75	
Mount: C-Mount	
Regulatory Compliance	
RoHS 2015: Exempt	
Certificate of Conformance: View	
REACH 241: Contains SVHC(s)	

Product Details

CS-Mount lenses are not compatible with C-Mount cameras.

- Low Distortion and Day/Night Options
- Focal Lengths from 4.4mm - 90mm
- C-Mount Versions

Megapixel Varifocal Lenses are the ideal choice when you need a specific field of view that corresponds to a non-standard focal length. They make system integration straightforward while allowing for fine tuning, and also create the flexibility so the lenses can be integrated across multiple applications. Day/Night varifocal lenses are the perfect choice when you need to extend your imaging system into the NIR without sacrificing visible imaging. Megapixel Varifocal Lenses have C-Mount versions. The lenses feature focal lengths from 4.4 to 90mm.