

45° Full Fan Angle Laser Line Generator Lens



Powell Lenses

Stock **#43-474** ☐ In Stock

-

1

+

C\$326.20

ADD TO CART

Qty 1-5
C\$326.20

Qty 6+
C\$261.10

Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 8.90 +0.00/-0.15
Substrate: ☐ N-SF6
Coating: VIS-NIR (450-900nm)
Type:

Beam Shaping Lens
Wavelength Range (nm): 450 - 900
Coating Specification: BBAR @ 450 - 900nm
Height (mm): 8.90 +0.00/-2.00
Index of Refraction n_d: 1.805
Fan Angle (°): 45.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View