

TECHSPEC® 45° AOI, 25.0mm Square, Hot Mirror



TECHSPEC High Performance Hot Mirrors

Stock **#64-468** ☐ In Stock

1

C\$74.20

ADD TO CART

Qty 1-9

C\$74.20

Qty 10+

C\$65.38

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):
45

Coating:
Hot Mirror, 45°

Substrate: ☐
[BOROFLOAT®](#)

Dimensions (mm):

25.0 x 25.0
Surface Quality: 80-50
Thickness (mm): 3.30
Thickness Tolerance (mm): ±0.2
Type: Dichroic Filter
Dimensional Tolerance (mm): +0.0/-0.2
Coating Specification: T _{avg} >85% @ 400 - 690nm, R _{avg} >95% @ 750 - 1125nm AR: R _{avg} <1% @ 400 - 700nm
Wavelength Range (nm): 400 - 1125
Surface Flatness (P-V): 4 - 6λ
Coating Type: Dielectric

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant