

4.61mm FL, High Resolution, f/1.6, Micro Video Lens



Stock #17-159 □ In Stock

-

1

+

C\$95.20

ADD TO CART

Qty 1+

C\$95.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Length (mm):
29.70

Maximum Diameter (mm):
19

Maximum Image Circle (mm):
8.00

Note:
High Resolution

Type:
M12 Imaging Lens

Focal Length FL (mm): 4.61
Maximum Sensor Format: 1/2"
Working Distance (mm): 400 - ∞
Mount: M12 x0.5 (S-Mount)
Aperture (f/#): f/1.6
IR Cut Filter: No
Lens Wavelength Range: VIS

Regulatory Compliance

Certificate of Conformance: View
--