

473nm 50mW Low Cost Turnkey Laser



Low Cost Turnkey Laser & Power Supply (Included)



Stock **#35-070** ☐ In Stock

1

C\$6,230.00

ADD TO CART

Qty 1-9
C\$6,230.00
Qty 10+
C\$5,607.00
Volume Pricing
Request Quote

Get Product Downloads



Output Power (mW):
50

Pointing Stability after Warm Up (mrad°C):
<0.05

Polarization:

>100:1
Power Stability (%) : <2% RMS over 4 hours
Dimensions (mm) : 143.5 x 73.0 x 46.2
Wavelength (nm) : 473.00
Mode Quality, M² : <1.2
Wavelength Tolerance (nm) : ±1
Power Supply : 153.0 x 155.0 x 92.0
Warm-Up Time (minutes) : <10
Power Requirement : 85-264VAC
Modulation Frequency (kHz) : 1-10
Beam Diameter (mm) : 1.2
Output Type : Free Space
Type of Laser : Diode
Beam Divergence (mrad) : <1.5
Laser Class - CDRH : IIIb
Color : Blue
Beam Height from Base Plate (mm) : 24.8
Mean Time to Failure MTTF (hours) : >10,000

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 233 : Compliant