

48mm Outer Dia., Zero Aperture, Burnished Steel Leaves



Zero Series

Stock **#57-590** ☐ In Stock

-

1

+

C\$154.00

ADD TO CART

Qty 1-4

C\$154.00

Qty 5+

C\$135.94

Volume Pricing

[Request Quote](#)

Get Product Downloads

Minimum Aperture (mm):

0.00

Maximum Aperture (mm):

30.0

Outer Diameter (mm):

48.0

Construction:

Anodized Aluminum Alloy, Burnished Leaves
Full Angular Range of Lever (°): 100.00
Lever Length (mm): 11.00
Lever Position (mm): 2.50
Lever Size (mm): 6.00 x 1.00
Number of Leaves: Two sets of 7
Operating Temperature (°C): <250
Pin Thread & Pitch: N/A
Thickness (mm): 5.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant