

4mm 2 MegaPixel Fixed Focal Length Lens



4mm Fixed Focal Length, #14-394

Stock **#14-394** 5 In Stock

-

1

+

C\$959⁰⁰

ADD TO CART

Volume Pricing	
Qty 1+	C\$959.00 each
Need More?	Request Quote

Product Downloads

General	
Fixed Focal Length Lens	Type:
Physical & Mechanical Properties	
Variable	Iris Option:
35.97	Length (mm):
44.5	Maximum Diameter (mm):

130	Weight (g):
Optical Properties	
77.4°	Horizontal Field of View @ Max Sensor Format:
77.4°	Horizontal Field of View, 1/2" Sensor:
61.93°	Horizontal Field of View, 1/3" Sensor:
43.6°	Horizontal Field of View, 1/4" Sensor:
8.00	Maximum Image Circle (mm):
4.00	Focal Length FL (mm):
100 - ∞	Working Distance (mm):
f/2 - f/16	Aperture (f/#):
<-2.8	Distortion (%):
VS	Lens Wavelength Range:
Sensor	
1/2"	Maximum Sensor Format:
Threading & Mounting	
C-Mount	Mount:
Regulatory Compliance	
View	Certificate of Conformance:

Product Details

- 2 MegaPixel Resolution Design
- Lockable, Manual Focus and Iris
- Fixed Focal Lengths from 4 to 50mm
- C-Mount Lens Mount

2 MegaPixel Fixed Focal Length Lenses are designed for machine vision applications that require higher resolution than the [MegaPixel Fixed Focal Length Lenses](#). These C-Mount lenses feature built-in locking mechanisms for the manual focus and iris, preventing unwanted adjustments. Lenses with a fixed focal length from 4 to 50mm are available with the 6 to 50mm lenses featuring M30.5 x 0.5 filter thread, allowing the use of [machine vision filters](#). 2 MegaPixel Fixed Focal Length Lenses cover 1/2" and 2/3" sensor sizes, making them compatible with all of our [2MP machine vision cameras](#). These lenses are used in industrial machine vision, [factory automation](#), and factory inspection applications.