

4" LED Ring Light 520nm with Barrel Mount, Strobed

See More by [Advanced Illumination](#)



Stock #83-243 [CONTACT US](#)

- 1 + **C\$1,600.20**

ADD TO CART

Qty 1+
C\$1,600.20

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: Green
Diameter (mm): 100.00
Height (mm): 33.8
Inner Diameter (mm): 55.5

Model Number: RL4260B-520-IS
Mount: Barrel Mount
Operating Temperature (°C): 0 to 65
Dimensions (mm): 100 Dia x 33.8 T
Mounting Threads: M4 x4
Wavelength (nm): 520.00
Working Distance (inches): 4.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Light Distribution (%): ±10 edge to edge (dependent on working distance)
Number of LEDs: 60.00
Number of Channels: 1.00
Field Coverage (mm): 43.18 (1.7 inches)
Maximum Trigger Frequency (Hz): 30.00
Strobe Duration (µs): 30 - 300
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Ring Light
Illumination Mode: Strobed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View