

4" x 4" Green Advanced Illumination Side-Fired Backlight

See More by [Advanced Illumination](#)



Stock #88-506 [CONTACT US](#)

-

1

+

C\$1,050.00

ADD TO CART

Qty 1+
C\$1,050.00

Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color: Green
Model Number: BX0404-530-IC
Operating Temperature (°C): 0 to 60
Dimensions (mm): 165.9 L x 165.9 W x 20.1 D

Wavelength (nm): 530.00
LED Lifetime (hours): 50,000
Power Supply: Power Supply Required and Sold Separately. USA: #66-855 Europe: #66-855 Japan: #66-855 Korea: #33-773 China: #66-855
Number of Channels: 1.00
Active Area (inches): 4 x 4
Type of Illumination: LED Illuminator
Manufacturer: Advanced Illumination
Geometry: Backlight
Illumination Mode: Constant

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Contains SVHC(s)