


4" x 5" Size, Plastic Optical Window



Stock **#43-928** ☐ In Stock

-

1

+

C\$59.50

ADD TO CART

Qty 1-49
C\$59.50
Qty 50+
C\$47.60
Volume Pricing
Request Quote

Get Product Downloads



Abbe Number (v_d):
57.00

Dimensions (mm):
101.60 x 127.00

Dimensions (inches):
4.00 x 5.00

Thickness (mm):

1.50 ±0.15
Coating: Uncoated
Density (g/cm³): 1.320
Index of Refraction n_d: 1.501
Operating Temperature (°C): 100 Continuous, 130 for 1 hour
Substrate: Thermoset ADC (CR-39®)
Transmission (%): >90 (typical)
Type: Protective Window
Wavelength Range (nm): 400 - 1500
Length (mm): 127.00
Width (mm): 101.60

Regulatory Compliance

RoHS 2015: Compliant
Reach 223: Compliant
Certificate of Conformance: View