

4X DIN Achromatic Commercial Grade Objective



4XDIN Achromatic Commercial Grade Objective, #43-902

Stock **#43-902** ☐ In Stock

1 **C\$119.00**

ADD TO CART

Qty 1+

C\$119.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Effective Focal Length EFL (mm):
31.04

Length excluding Threads (mm):
26.00

Magnification:
4X

Maximum Diameter (mm):
24

Numerical Aperture NA:
0.10

Mounting Threads: 0.7965-36 TPI, 55° Whitworth
Type: Achromatic
Operating Temperature (°C): 5 to 40
Storage Temperature (°C): -20 to 60
Working Distance (mm): 18.8
Style: Finite Conjugate
Parfocal Length (mm): 44.8
Immersion Liquid: N/A
Operating Relative Humidity: 45% to 85%

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View