

TECHSPEC® 50.0mm Dia. x 150.0mm FL, Uncoated, Plano-Convex Lens



Stock **#32-974** [CONTACT US](#)

[Other Coating Options](#)



1



C\$60.20

ADD TO CART

Qty 1-9

C\$60.20

Qty 10+

C\$54.25

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.025

Effective Focal Length EFL (mm):
150.00 @587.6nm

Back Focal Length BFL (mm): 144.07
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 9.00 ±0.10
Edge Thickness ET (mm): 4.86
Radius R₁ (mm): 77.52
Clear Aperture CA (mm): 49
f#: 3
Numerical Aperture NA: 0.17
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
