

50.8mm Clear Aperture, 2 Arcsec, Aluminum Retroreflector



Stock **#49-667** ☐ In Stock

1 **C\$1,890.00**

ADD TO CART

Qty 1+
C\$1,890.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 2.00
Clear Aperture CA (mm): 50.8
Coating: Enhanced Aluminum (450-650nm)
Diameter (mm): 76.20
Exiting Wavefront Accuracy: 0.5λ

Substrate:  BOROFLOAT®
Surface Quality: 80-50
Mounting Threads: (6) ¼-20, (5) M6 x 1.0
Type: Retroreflector
Dimensional Tolerance (mm): ±1.6
Image Orientation: Left-Handed
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
REACH 201: Compliant
Certificate of Conformance: View