

50.8mm Clear Aperture, 5 Arcsec, Aluminum Retroreflector



Stock **#49-668** ☐ In Stock

1 **C\$1,456.00**

ADD TO CART

Qty 1+
C\$1,456.00

Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec): 5.00
Clear Aperture CA (mm): 50.8
Coating: Enhanced Aluminum (450-650nm)
Diameter (mm): 76.20
Exiting Wavefront Accuracy: 1.25λ

Substrate:  BOROFLOAT®

Surface Quality:
80-50

Mounting Threads:
(6) ¼-20, (5) M6 x 1.0

Type:
Retroreflector

Dimensional Tolerance (mm):
±1.6

Image Orientation:
Left-Handed

Ray Deviation (°):
180

Wavelength Range (nm):
400 - 700

Regulatory Compliance

RoHS 2015:
[Compliant](#)

REACH 201:
[Compliant](#)

Certificate of Conformance:
[View](#)