

## 50/50.8mm ID, Precision Gimbal Mount, Quick Start Optical Mounts



#17-534 and #17-513



Stock **#17-518** [CONTACT US](#)

- 1 +

C\$716.66

ADD TO CART

|           |
|-----------|
| Qty 1+    |
| C\$716.66 |

|                               |
|-------------------------------|
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Type:  
Adjustable - Gimbal

Type of Optics:  
Circular

Size of Compatible Optics (mm):  
50.0 - 50.8

Clear Aperture CA (mm):  
46.0

|                                                                                                                                  |
|----------------------------------------------------------------------------------------------------------------------------------|
| <b>Coarse Rotation (°):</b><br>360                                                                                               |
| <b>Fine Tilt Angle (°):</b><br>±4                                                                                                |
| <b>Fine Tip Angle (°):</b><br>±4                                                                                                 |
| <b>Contents of Kit:</b><br><a href="#">#55-000</a> , <a href="#">#16-310</a> , <a href="#">#16-321</a> , <a href="#">#15-848</a> |
| <b>Compatible Post:</b><br>M6 x 1.0                                                                                              |
| <b>Max. Thickness of Compatible Optics (mm):</b><br>11.0                                                                         |
| <b>Optical Axis Height (mm):</b><br>127.00                                                                                       |
| <b>Type of Adjustment Screws:</b><br>Micrometer                                                                                  |
| <b>Post Diameter (mm):</b><br>25.4                                                                                               |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 233:</b><br><a href="#">Compliant</a>             |