

50mm 2 MegaPixel Fixed Focal Length Lens



50mm Fixed Focal Length, #14-401

Stock **#14-401** ☐ In Stock

-

1

+

C\$595.00

ADD TO CART

Qty 1+

C\$595.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Iris Option:
Variable

Length (mm):
33.65

Horizontal Field of View, 1/2" Sensor:
7.46°

Horizontal Field of View, 2/3" Sensor:
10.2°

Filter Thread:
M30.5 x0.50 (Female)

Maximum Diameter (mm): 32.5
Weight (g): 80
Horizontal Field of View, 1/3" Sensor: 5.6°
Maximum Image Circle (mm): 11.00
Horizontal Field of View @ Max Sensor Format: 10.2°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 50.00
Maximum Sensor Format: 2/3"
Working Distance (mm): 1000 - ∞
Mount: C-Mount
Aperture (f/#): f/2 - f/16
Distortion (%): <0.4
Horizontal Field of View, 1/4" Sensor: 3.67°
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View