

TECHSPEC®

50mm Dia., 0.50 Numerical Aperture, Uncoated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-440-INK** [CONTACT US](#)

[Other Coating Options](#)

-

1

+

C\$798.00

ADD TO CART

Qty 1-5

C\$798.00

Qty 6+

C\$638.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
50.00 ±0.025

Effective Focal Length EFL (mm):
50.00 @ 587.6nm

Numerical Aperture NA:
0.50

Back Focal Length BFL (mm): 42.77
Substrate:  N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 45.00
Edge Thickness ET (mm): 5.08
Center Thickness CT (mm): 13.06 ±0.10
f/#: 1.00
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View