


50mm Dia., 0.7mm Thick, EAGLE XG® Window



Stock **#18-294** ☐ In Stock

-

1

+

C\$50.40

ADD TO CART

Qty 1-5
C\$50.40
Qty 6+
C\$40.60
Volume Pricing
Request Quote

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90

Clear Aperture CA (mm):
45.00

Diameter (mm):

50.00 ±0.25
Thickness (mm): 0.70 ±0.07
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 3.17 (0 to +300°C)
Density (g/cm³): 2.38
Edges: Fine Ground
Index of Refraction n_d: 1.51
Poisson's Ratio: 0.23
Substrate: EAGLE XG®
Surface Quality: 80-50
Type: Protective Window
Wavelength Range (nm): 350 - 2000
Young's Modulus (GPa): 73.6

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant