

TECHSPEC[®] 50mm Dia., Enhanced Deep UV (DUV) Mirror



Precision Ultraviolet Mirrors

Stock #18-748 ☐ In Stock

-

1

+

C\$540.40

ADD TO CART

Qty 1-5

C\$540.40

Qty 6+

C\$432.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.2

Surface Flatness (P-V):
λ/10

Substrate: ☐
[Fused Silica](#) (Corning 7980)

Back Surface: Ground
Surface Quality: 10-5
Coating Specification: R _{avg} ≥92% @ 190 - 250nm R _{avg} ≥83% @ 250 - 900nm
Coating: Enhanced Aluminum (190-900nm)
Coating Type: Metal
Angle of Incidence (°): 0
Clear Aperture (%): 90
Design Wavelength DWL (nm): 190
Parallelism (arcmin): <3
Thickness (mm): 10.00 ±0.20
Type: Flat Mirror
Wavelength Range (nm): 190 - 900
Vacuum Compatibility: 10 ⁻⁷ Torr

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View