

TECHSPEC® 50mm Dia Silver, 4-6λ Mirror



Stock **#89-494** ☐ In Stock

1

C\$65.10

ADD TO CART

Qty 1-5

C\$65.10

Qty 6+

C\$49.70

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
50.00 ±0.25

Surface Flatness (P-V):
4 - 6λ

Substrate: ☐
Float Glass

Surface Quality:
60-40

Dimensional Tolerance (mm): ±0.25
Coating Specification: R_{avg} >98% @450 - 2000nm R_{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 47.50
Edges: Ground, 0.5mm Maximum Edge Chip
Thickness (mm): 3.00 nominal
Type: Flat Mirror
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant