

TECHSPEC® 5.0mm Dia. x 10.0mm FL, Uncoated, Plano-Convex Lens



Stock **#45-229** ☐ In Stock
[Other Coating Options](#)

1 **C\$49.00**

ADD TO CART

Qty 1-9
C\$49.00
Qty 10+
C\$44.10
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
5.00 +0.0/-0.025

Effective Focal Length EFL (mm):
10.00 @ 587.6nm

Back Focal Length BFL (mm): 8.91
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <3
Center Thickness CT (mm): 1.64 ±0.05
Edge Thickness ET (mm): 1.00
Radius R₁ (mm): 5.17
Clear Aperture CA (mm): 4.5
f#: 2
Numerical Aperture NA: 0.25
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View
