

TECHSPEC® 50mm Dia. x 2.0mm Thickness Uncoated, Silicon Window



TECHSPEC Silicon (Si) Windows

Stock #68-530

CONTACT US



1



C\$395.50

ADD TO CART

Qty 1-10

C\$395.50

Qty 11+

C\$356.30

Volume Pricing

[Request Quote](#)

Get Product Downloads



Bevel:
Protective as needed

Clear Aperture (%):
90.00

Clear Aperture CA (mm):
45.00

Diameter (mm): 50.00 +0.0/-0.1
Thickness (mm): 2.00 ±0.1
Coating: Uncoated
Coefficient of Thermal Expansion CTE (10⁻⁶/°C): 2.55
Density (g/cm³): 2.33
Edges: Fine Ground
Index of Refraction n_d: 3.422 @ 5µm
Knoop Hardness (kg/mm²): 1150
Parallelism (arcmin): <3
Poisson's Ratio: 0.265
Substrate: Silicon (Si)
Surface Flatness (P-V): 1λ
Surface Quality: 60-40
Type: Protective Window
Wavelength Range (nm): 1200 - 7000
Young's Modulus (GPa): 140

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View