

## 50mm Diameter Mounted 0.04-3.0 OD, Circular Variable Neutral Density (ND) Filter



Mounted Circular Variable Neutral Density (ND) Filters

Stock **#54-536** ☐ In Stock

-

1

+

C\$567.00

ADD TO CART

Qty 1-10

C\$567.00

Qty 11+

C\$510.30

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):  
0.00

Optical Density OD (Average):  
0.04 - 3.0

Substrate: ☐  
[B270](#)

Inner Diameter (mm):

|                                                                              |
|------------------------------------------------------------------------------|
| 7.5                                                                          |
| <b>Coating:</b><br>Variable                                                  |
| <b>Outer Diameter (mm):</b><br>50.0                                          |
| <b>Surface Quality:</b><br>60-40                                             |
| <b>Thickness (mm):</b><br>1.52                                               |
| <b>Thickness Tolerance (mm):</b><br>±0.25                                    |
| <b>Type:</b><br>Neutral Density Filter                                       |
| <b>Blocking Wavelength Range (nm):</b><br>400 - 700                          |
| <b>Parallelism (arcmin):</b><br>±3                                           |
| <b>Dimensional Tolerance (mm):</b><br>±0.10 ID, ±0.20 OD                     |
| <b>Optical Density Tolerance (%):</b><br>±5                                  |
| <b>Linearity (%):</b><br>±5                                                  |
| <b>Coating Specification:</b><br>Continuously Variable Inconel from 0 - 270° |
| <b>Mount:</b><br>Mounted                                                     |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Exempt</a>                     |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |