

50mm Diameter x 44mm FL, PCX Condenser Lens



Stock **#43-593** ☐ In Stock
[Other Coating Options](#)

1 **C\$58.80**

ADD TO CART

Qty 1-10
C\$58.80
Qty 11+
C\$51.80
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm):
50.00 +0.2/-0.4

Effective Focal Length EFL (mm):
44.00

Numerical Aperture NA:
0.57

Substrate: ☐

[B270](#)

Focal Length Tolerance (%):
±7

Coating:
Uncoated

Centering (arcmin):
≤25

Surface Quality:
80-50 (typical)

Center Thickness CT (mm):
18.90 +1.0/-0.4

f/#:
0.88

Bevel:
Protective bevel as needed

Radius R₂ (mm):
Plano

Shape of Back Surface:
Plano

Type:
Condenser Lens

Wavelength Range (nm):
350 - 2500

Conjugate Distance:
Infinite

Regulatory Compliance

RoHS:
[Exempt](#)

Certificate of Conformance:
[View](#)