

50mm FL F-Mount Lens for 46mm Sensors



Stock **#85-192** ☐ In Stock

[Similar Products](#)

⊖ 1 ⊕

C\$2,625.00

ADD TO CART

Qty 1+
C\$2,625.00

Volume Pricing
Request Quote

Get Product Downloads

Field of View @ Min Working Distance (mm):
169.00

Iris Option:
Variable

Length (mm):
77.00

Filter Thread:
M52 x 0.75

Maximum Diameter (mm):
54.0

Weight (g): 460.00
Maximum Image Circle (mm): 43.30
Horizontal Field of View, 35mm Sensor: 38.6°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 50.00
Maximum Sensor Format: 35mm (43.3mm Image Circle)
Working Distance (mm): 260 - ∞
Mount: F-Mount
Aperture (f/#): f/2.8 - f/22
Distortion (%): <-0.1
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)