

TECHSPEC® 50mm NIR, Polarizing Cube Beamsplitter



TECHSPEC® Broadband Polarizing Cube Beamsplitters

Stock **#65-606** ☒ In Stock

⊖ 1 ⊕ **C\$1,365.00**

ADD TO CART

Qty 1-5
C\$1,365.00
Qty 6+
C\$1,092.00
Volume Pricing
Request Quote

Get Product Downloads



Beam Deviation (arcmin):
±3

Clear Aperture (%):
90

Coating Specification:
R_{avg} <0.5% @ 700 - 1100nm

Construction: Cube
Dimensions (mm): 50.0 x 50.0 x 50.0 ±0.1
Extinction Ratio: 500:1
P-Polarization Transmission (%): >90
S-Polarization Reflection (%): >99
Substrate: ☐ N-SF11
Surface Flatness (P-V): λ/8
Surface Quality: 40-20
Type: Linear Polarizer
Wavelength Range (nm): 700 - 1100

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View