

50mm Square, Cyan Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#39-912** ☐ In Stock



1



C\$55.30

ADD TO CART

Qty 1-24

C\$55.30

Qty 25+

C\$48.72

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Angle of Incidence (°):
0

Cut-Off Wavelength (nm):
590.00

Substrate:  BOROFLOAT®
Length (mm): 50.00
Operating Temperature (°C): <100
Coating: Subtractive Color
Color: Cyan
Surface Quality: 80-50
Thickness (mm): 2.00 Nominal
Type: Dichroic Filter
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.25
Clear Aperture (%): ≥85
Coating Specification: T _{avg} >80% @ 400 - 550nm T _{avg} <1.0% @ 640 - 740nm
Cut-Off Wavelength Tolerance (µm): 0.015

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant