

50mm Square, Yellow Dichroic Filter



Additive and Subtractive Dichroic Color Filters

Stock **#30-637** ☐ In Stock



1



C\$55.30

ADD TO CART

Qty 1-24

C\$55.30

Qty 25+

C\$48.72

Volume Pricing

[Request Quote](#)

Get Product Downloads



Dimensions (mm):
50.0 x 50.0

Angle of Incidence (°):
0

Cut-On Wavelength (nm):
520.00

Substrate:  BOROFLOAT®

Length (mm):
50.00

Operating Temperature (°C):
<100

Coating:
Subtractive Color

Color:
Yellow

Surface Quality:
80-50

Thickness (mm):
2.00 Nominal

Type:
Dichroic Filter

Width (mm):
50.00

Dimensional Tolerance (mm):
±0.25

Clear Aperture (%):
≥85

Cut-On Wavelength Tolerance (µm):
0.015

Coating Specification:
T_{avg} <1.0% @ 400 - 475nm
T_{avg} >80% @ 550 - 750nm

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Compliant](#)