

TECHSPEC® 50R/50T, C-Mounted Standard Plate Beamsplitter



Stock **#54-824** ☒ In Stock

1

C\$413.00

ADD TO CART

Qty 1-4

C\$413.00

Qty 5+

C\$362.60

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating Specification:
Surface 2: $\lambda/4$ MgF₂ Anti-Reflection

Construction:
Plate

Dimensional Tolerance (mm):
 ± 0.375

Extension Length (mm):
38.0

Housing: Black Anodized Aluminum
Housing Dimension: 38 x 38 x 50
Mount: C-Mount Enclosure
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thread Type: C-Mount (1" x 32 TPI)
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700
Beamsplitter Included: #45-325

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View