

50X Mitutoyo BD Plan Apo Objective

See More by [Mitutoyo](#)



Mitutoyo Brightfield and Darkfield (BD) Infinity Corrected Objectives

Stock **#18-407** 2 In Stock

-

1

+

C\$6,055^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	C\$6,055.00 each
Need More?	Request Quote

Product Downloads

General	
378-835-7	Model Number:
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm	
Microscope Objective	Type:
Infinity Corrected	Style:
	Manufacturer:


Mitutoyo	
Note: #18-653 or #18-652 are required for darkfield operation.	
Physical & Mechanical Properties	
82.00	Length excluding Threads (mm):
44	Maximum Diameter (mm):
440	Weight (g):
Optical Properties	
N/A	Compatible Cover Glass Thickness (mm):
4.00	Focal Length FL (mm):
50X	Magnification:
0.55	Numerical Aperture NA:
0.5	Resolving Power (μm):
0.90	Depth of Field (μm):
0.48	Field of View, 24 Diameter Field Eyepiece (mm):
13	Working Distance (mm):
435 - 655	Wavelength Range (nm):
95	Parfocal Length (mm):
N/A	Immersion Liquid:
Sensor	
2/3"	Maximum Sensor Format:
Threading & Mounting	
M40 x 36 TPI	Mounting Threads:
Environmental & Durability Factors	
+5 to +40	Operating Temperature (°C):
Regulatory Compliance	
Exempt	RoHS 2015:
View	Certificate of Conformance:
Contains SVHC(s)	REACH 241:

Product Details


- Ideal for Brightfield and Darkfield Mcroscopy Applications
- Long Working Distances and High Numerical Apertures
- Plan Apochromat Design

Mitutoyo Brightfield and Darkfield (BD) InfinityCorrected Objectives offer long working distances with high numerical apertures. The high-quality plan apochromatic design allows these objectives to maintain high numerical apertures and contrast while correcting chromatic aberration in the visible wavelength region. These objectives feature M40 x36TPI mounting threads. Mitutoyo Brightfield and Darkfield (BD) InfinityCorrected Objectives are optimized for both brightfield and darkfield illumination for applications including surface inspection and advanced life science microscopy.

Technical Information



Stock No.	BD Plan Apo	A	B	C	D	E	F	W.D.
#18-402	2X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-403	5X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-404	7.5X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-405	10X	61.0	4.0	40.0	37.0	42.0	44.0	34.0
#18-406	20X	75.0	7.0	40.0	32.0	42.0	44.0	20.0
#18-407	50X	82.0	8.5	40.0	32.0	42.0	44.0	13.0
#18-408	100X	89.0	10.0	40.0	31.5	42.0	44.0	6.0
Stock No.	BD Plan Apo SL	A	B	C	D	E	F	W.D.
#18-409	20XSL	64.5	7.5	40.0	31.0	42.0	44.0	30.5
#18-410	50XSL	75.0	7.0	40.0	32.0	42.0	44.0	20.0
Stock No.	BD Plan APO HR	A	B	C	D	E	F	W.D.
#18-411	50XHR	89.9	4.8	40.0	32.0	42.0	44.0	5.2
#18-412	100XHR	93.7	4.7	40.0	32.0	42.0	44.0	1.3



Units: mm